

Specification Sheet

Part Number: GT.75X1800



Features quick release for repetitive access to cable and wire.
Can be opened and closed numerous times without failure.
Adjustable so one size can accommodate multiple bundle sizes.

Grip Tie Roll, 180" Long, 0.75" Wide, PA6/PP, Black, 1/pkg

Article Number 854-44384

Type GT.75X180

Color Black (BK)

Quantity Per bag

Product Description For custom-cut lengths, HellermannTyton offers the hook and loop strap in various colors in a 5 yard roll and our stand black up to a 25 yard roll. Ideal for job site applications, desired lengths can be cut on the spot. The Grip Tie is reusable, adjustable, releasable, and easy to install.

Short Description Grip Tie Roll, 180" Long, 0.75" Wide, PA6/PP, Black, 1/pkg

Global Part Name GT.75X180

Length L (Imperial) 15.0

Length L (Metric) 4.5

Width W (Imperial) 0.75

Width W (Metric) 19.05

Material Polyethylene (PE) Polyamide (PA)

Material Shortcut PA PE

UV Resistant (Yes/No) No

Reach Compliant (Article 33) No

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity (Imperial) 1

Package Quantity (Metric) 1

Customs Number 3926909988

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)