



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GT4LWMV 2X4 Lensed TROFFER4, (4) *Lithonia Lighting*

Catalog Number	GT4LWMV
Manufacturer	Lithonia Lighting
Description	Lensed Troffer, T4 Bulb Shape, 48 In Length, 24 In Width, 3-1/8 In/7.9 CM Height, 120 to 277 V, 32 W, Electronic Ballast, Instant, White, 2850 LM Brightness (Lumens), Bi-Pin Base, 4100 K, 4 Lamps, 1 Ballasts, Steel Housing Material, Baked White Enamel, Recessed Mount, 23.7 LB/Ea
Weight per unit	23.7 (lbs/each)
Product Category	Fluorescent Recessed Architect

Features

Hardware	Yes
Lamp Included	Yes
Lamp Type	Fluorescent
Material	Steel
Maximum Operating Temperature	25
pallet quantity	28
Power Source	Hardwired
Shape	Rectangular
Socket Type	Bi-pin: Single
Warranty	2
Wattage	128

Material, Color, and Finish

Lens Color	Clear
Style	Traditional

Descriptions

Description	2X4 LENSED TROFFER4, (4)
extra long description	LITH GT4LW MV Lensed Troffer, 2FT x

Manufacturer Information

GTIN	00745975081707
UPC	745975081707

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Troffer

Trade Size

aperture size	2x4
---------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	23.7

Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	UL