

Eaton GUAB16

Catalog Number: GUAB16

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, B shape, 1/2"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover	GUAB16
	UPC
	782274461205
Product Length/Depth	Product Height
3.5 in	4.38 in
Product Width	Product Weight
2 in	3.07 lb

Product specifications

NEC hazardous rating

Class I, Division 1
Class I, Division 2
Class II, Division 1
Class II, Division 2
Class III

Trade size

1/2"

Shape

B

NEMA Rating

3
4
7
9

Cover opening diameter

3"

Area classification

Hazardous/Classified Locations

Material

Feraloy iron alloy

Standards type

NEC/CEC

Resources

Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

Specifications and datasheets

[Eaton Specification Sheet - GUAB16](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)