

# Eaton GUAC24

Catalog Number: GUAC24

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 2" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover	GUAC24
	<b>UPC</b>
	782274462202
<b>Product Length/Depth</b>	<b>Product Height</b>
4.25 in	2.5 in
<b>Product Width</b>	<b>Product Weight</b>
2 in	1.76 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

## Product specifications

### Shape

C

### Trade size

3/4"

### Cover opening diameter

2"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

### Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

### Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

### Specifications and datasheets

[Eaton Specification Sheet - GUAC24](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)