

# Eaton GUAN36

Catalog Number: GUAN36

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, N shape, 1"

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover	GUAN36
	UPC
	782274466606
Product Length/Depth	Product Height
4.5 in	4.5 in
Product Width	Product Weight
2.31 in	3 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

## Product specifications

### Material

Feraloy iron alloy

### Shape

N

### Trade size

1"

### Cover opening diameter

3"

## Resources

### Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

### Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

### Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

### Specifications and datasheets

[Eaton Specification Sheet - GUAN36](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)