

Eaton GUAX59

Catalog Number: GUAX59

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 5" cover opening diameter, Feraloy iron alloy, X shape, 1-1/2"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover	GUAX59
	UPC
	782274469409
Product Length/Depth	Product Height
7.88 in	7.88 in
Product Width	Product Weight
4.03 in	12.56 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

7

9

Product specifications

Shape

X

Trade size

1-1/2"

Cover opening diameter

5"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

Specifications and datasheets

[Eaton Specification Sheet - GUAX59](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)