#### H221 - SHALLOW IC HOUSING

Source	Model	Description
H221 24P HOUSING TRIM	IC Housing with hanger bars, junction box and magnetic ballast Flush Diffuser Trim 8-3/8"L x 4-5/8"D x 3-1/2"H (213mm x 117mm x 89mm) 5-1/2" x 9-1/4" (140mm x 235mm)	Integral 120V 60 Hz magnetic fluorescent ballast for one 13W Twin Tube 2-pin Compact Fluorescent lamp (F13TT, GX23 base). Junction box listed for through branch circuit wiring and has two 3/4" and five 1/2" knockouts. Bar hangers will span 24" joists. 3-1/2" height for use in shallow ceilings. May be installed in IC applications. May be installed in Ceiling or wall. UL/cUL Damp location listed, Feed through Listed, Replacement Lamp: Available by others or as Halo #Z63



## H2925T, H2925TW, H2925PL - BRICK LIGHT / AISLE LIGHT

Source	Description
	With thermal protector, brown die cast trim, flat unbreakable lens and tamper proof screws. (Non-IC)
H2925T	Incandescent 20W T6 1/2 lamps (Halo Z7). (Damp location listed)
H2925TW	Incandescent 20W T6 1/2 lamps (Halo Z7). (Wet location listed)
H2925PL	7W 2-pin, G23 base compact fluorescent lamps or 9W lamp. (UL/cUL Wet location listed)
SD2925	Tamper proof screwdriver accessory
HOUSING	7-3/8"L x 3-1/2"D x 2-1/4"H (187mm x 89mm x 57mm)
TRIM	8-7/8"L x 3-1/2"H (225mm x 89mm)



## H2926TW - BRICK LIGHT / AISLE LIGHT

Source	Description
	With thermal protector, brown die cast trim, glare reducing shade and tamper proof screws. (Non-IC)
H2926TW ACCESSORY	Incandescent 20W T6 1/2 lamps (Halo Z7). (Wet location listed) Tamper proof screwdriver accessory
HOUSING	7-3/8"L x 3-1/2"D x 2-1/4"H (187mm x 89mm x 57mm)
TRIM	8-7/8"L x 3-1/2"H (225mm x 89mm)
	8-7/8"L x 3-1/2"H (225mm x 89mm)



## H2920ICT - STEP LIGHT

Source	Description
H2920ICT	Step Light with white louver trim. Wiring connections are made in fixture. 25W A19 lamp. (IP Rated)
HOUSING	8"L x 3-1/2"D x 4-1/2"H (203mm x 89mm x 114mm)
TRIM	9-3/8"L x 5-3/4"H (238mm x 146mm)
FINISH	White (P)



#### H2922ICT - STEP LIGHT

Source	Description
H2922ICT	Step Light with white louver trim. Fixture is prewired to junction box. UL/cUL listed junction box rated for feed through. 25W A19 lamp. IC rated for direct contact with insulation and combustible materials. (IP Rated)
HOUSING TRIM FINISH	11-5/8"L x 3-1/2"D x 5-1/2"H (295mm x 89mm x 140mm) 9-3/8"L x 5-3/4"H (238mm x 146mm) White (P)



## H2922-120PL - STEP LIGHT

TEACH TEACH OF EIGHT	
Source	Description
H2922-120PL	Step Light with white louver trim. Fixture is prewired to junction box. UL/cUL listed junction box rated for feed through. Integral 120V, 60 Hz magnetic ballast. (5W / 7W / 9W Twin Tube 2-pin CFL)
HOUSING TRIM FINISH	11-5/8"L x 3-1/2"D x 5-1/2"H (295mm x 89mm x 140mm) 9-3/8"L x 5-3/4"H (238mm x 146mm) White (P)

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.



#### H2900T - THRU-WALL LIGHT, NON-IC



#### H2932ICTW - LENSED WALL / STEP LIGHT

Source	Description
H2932ICTW	UL/cUL Listed for wall mounting in insulation. IC rated for direct contact with insulation and combustible material, UL/cUL listed for damp location; and feed through. (White trim with Albalite Glass Lens)
HOUSING	11-1/2"L (enclosure and J-Box) x 5-1/2"D x 3-1/2"H (292mm x 140mm x 89mm)
TRIM	5-3/4"L x 9-3/8"H (146mm x 238mm)
LAMP	25W, A19 max.
FINISH	White (P)



#### H2932T - CLOSET LIGHT / SHALLOW RECTANGLE, NON-IC

Source	Description
H2932T	White trim with albalite diffuser. Junction box rated for feed through branch applications. (For Non-Insulated Ceilings. UL/cUL Listed)
HOUSING	11-5/8"L x 3-1/2"D x 5-1/2"H (295mm x 89mm x 140mm)
TRIM	9-3/8"L x 5-3/4"H (238mm x 146mm)
LAMP	60W, A19 max.
FINISH	White (P)



#### H37T-401AL - HEAT LIGHT, NON-IC

Source	Description
H37T-401AL	For Non-Insulated Ceilings. IP Rated (Improper Lamp)
HOUSING	8"OD x 5-1/2"H (203mm x 140mm)
TRIM RING	Brushed Aluminum
LAMP	250W Infra-Red



# 477 - POWER-TRAC ADAPTER TRIM

Source	Description
477	Allows (120V) Trac Lampholders (150W max) to be used with recessed installations.
OD	(Use with H7T, H7ICT, H27T, H7RICT, H27RT and H44T housings)
FINISH	7-1/4" (184mm)
LINIOL	White with Black Baffle (477P), White with White Baffle (477W)



# DICHROIC COLOR FILTERS

Source	Model
L114	UV Filter
L120	Red
L121	Amber
L122	Yellow
L123	Green
L124	Daylight
L125	Blue
L127	Cosmetic Color Filters
L130	Yellow
	For low voltage MR16 units.



# OPTICAL LENSES

Source	Model
L110	Diffuse Sand Blasted Lens
L111	Soft Focus Textured Lens
L113	Prismatic Lens
L115	Linear Spread Lens
	For Low Voltage MR16 units

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.

#### **DESIGNER FINISH TRIM RINGS**

Source	Model	Description
TRM6P	White Metal	Metal 7 1/4" OD (184mm). (Compatible with 310*, 312*, 376, 378, 400, 404, 405, 406SC, 406RG, 409, 410,
TRM6C TRM6SN	Chrome Satin Nickel	416, 419, 420, 424, 425, 426*, 429*, 446, 448, 455CG, 455SC, 456P, 456W, 477, 478, 1412, 1416, 1475, 2412, 2416, 2475)
TRM6TBZ	Tuscan Bronze	
TRM6MB TRM7MB	Black Metal Black Plastic	*Supplied with TRM6P white metal trim rings (All others are supplied with white plastic trim rings)
TTTIVITIVID	Diack Flastic	



#### **OVERSIZED TRIM RINGS**

Source	Size	Description
OT400P OT403P	6" ID X 9-1/4" OD (152mm x 235mm) 6" ID X 8" OD (152mm x 203mm)	Oversized white metal trim ring. (May be used behind any Halo H7/H750 trim family) Oversized white plastic trim ring. (Compatible with 310, 312, 376, 378, 400, 404, 405, 406 (SC and RG only), 409, 410, 416, 419, 420, 424, 425, 426, 429, 446, 448, 477, 478, 1412, 1416, 1475, 2412, 2416, 2475)
ОТ999Р	4" ID x 5-3/4" OD (102mm x 146mm)	Oversized white metal trim ring. (Compatible with 990, 992, 993, 994, 996, 998, 999, 1419, 1420, 1421, 1493 and 1498)
OT460P	7-1/2" ID x 11-1/4" OD (191mm x 286mm)	Oversized white metal trim ring compatible with 466, 468 and 480 trims
OT490WH 800PGR	5-3/16" ID x 9-1/4" OD (132mm x 235mm) 7-1/2" ID x 8-5/8" OD (191mm x 219mm)	White aluminum ring use with ML7x LED modules: 600 Series, 900 Series and 1200 Series H800 oversized trim ring
OT500P	6" ID x 7 1/4" OD (152mm x 184mm)	Oversized white polymer trim ring for use with H5 series straight sided trims



## DESIGNER TRIM RINGS

Source	Size	Finishes	Description
TRM400	3-3/8" ID X 5-1/8" OD (86mm x 130mm)	PC - Polished Chrome BK - Black WH - White SN - Satin Nickel TBZ - Tuscan Bronze	For H4 LED TL4 Series LED Trims. Die cast trim ring replaces standard ring included with each trim. (Thin profile provides subtle ceiling appearance) 0.12" OD x 0.18" ID (4mm x 5mm)
TRM490	5-3/16" ID x 7-1/4" OD (132mm x 184mm)		For H7 LED 49x Series LED Trims. Die cast trim ring replaces standard ring included with each trim. (Thin profile provides subtle ceiling appearance) 0.12" OD x 0.18" ID (4mm x 5mm)



## **TRANSFORMERS**

Source	Description
H277 H347 H347200	Steps 277V line voltage down to 120V fixture operating voltage. 300VA max. (For use with Non-IC housings) Same as above but steps 347V down to 120V, 75 VA max. (For use with Non-IC housings) Same as above but steps 347V down to 120V, 200 VA max. (For use with Non-IC housings)



## HANGING BARS

Source	Description
HB224 HB424	One piece hanger bar for 24* maximum joist spacing. (Set of two) Two piece hanger bar for 24* maximum joist spacing. (Set of four pieces, order one HB424 per fixture)
	Hanger bars are compatible with the following housing families: M700, H800, H801, H802, H803, and H880E.



## SLOPE ADAPTERS

Description

White .050 spun aluminum. Available as shown in following table. Items in BOLD face are stocked  $\frac{\text{Slope}}{6^6 \text{ for H44}} \quad \frac{0^\circ}{\text{NSA68}} \quad \frac{5^\circ}{\text{NSA68}} \quad \frac{10^\circ}{\text{NSA68}}$ 

Slope	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
6" for H44	HSA680	HSA65	HSA610	HSA615	HSA620	HSA625	HSA630	HSA635	HSA640	
8" for H46		HSA85	HSA810	HSA815	HSA820	HSA825	HSA830	HSA835	HSA840	HSA845

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.

#### AIR-TITE™ Gaskets

#### Description

#### GA-ATH5-6PK

H5ICAT Air-Tite™ 6-pack gaskets for installation at finished ceiling opening

#### GA-ATH7-6PK

H7ICAT Air-Tite™ 6-pack gaskets for installation at finished ceiling opening



#### **TRIM GASKETS**

### Description

#### GA-ATTRIM-6PK

Accessory / spare trim gasket for use with H7 and EI/ET 700 family trims.



#### SOCKET EXTENDER

#### Description

#### H1999

For use with selected trims and housings. Extends lamp 1" (25mm)



#### MOUNTING CLIPS

#### Description

T-Bar attachment clips. Set of four. Order one set per fixture. Can also be used with HB424 and HB224 Hanger Bars

Hold down clips for non-remodel fixtures when hanger bars are not used. (Set of four)



### R LAMP ACCESSORY

#### Description

#### H930

R/PAR lamp aiming accessory for H7T, H7TNB, H7RT, H7ICT, H7ICAT, H7RICT, H7RICAT, H7ICTNB, H7ICATNB housings with 310 and 426 trims. Allows lamp to be aimed up to 30° from vertical and rotated 358°. See housing-trim selection for lamp listings



### SCREWDRIVER

# Description

#### SD2925

Screwdriver for tamper resistant screws supplied with H2925 and H2926 brick lights



#### 4 COIL SPRINGS

## Description

#### RS7H

LAMPS

Z21

Z26

Z31

Z40 Z45

Z121

Z131

Description

LOW VOLTAGE

Set of 4 coil springs for use with 301, 310, 401 and 426 trims in the H7 recessed housing family

12V Q50W MR16 NSP

12V Q50W MR16 NFL

12V Q75W MR16 NSP

12V Q75W MR16 FL

50W MR16/Q/10°/TL

50W MR16/Q/20°/TL

50W MR16/Q/40°/TL

(GE TURN-AND-LOCK BASE)

(GE TURN-AND-LOCK BASE)

(GE TURN-AND-LOCK BASE)

12V Q50W MR16 FL



#### LAMPS

# Description

#### COMPACT FLUORESCENT Z62 22W 15mm PL-C, Gx32d-2 Double Twin Tube Compact Fluorescent (2700°K)

28W 15mm PL-C Gx32d-3 Double Twin Z128 Tube (DTT) 2-Pin Compact Fluorescent (2700°K) 763 13W Twin Tube Compact Fluorescent, 2-pin, Gx23 (2700°K) 13W Double Twin Tube Compact Z64 Fluorescent, 2-pin, Gx23-2(2700°K) Z113E 13W Double Twin Tube (DTT) 4-Pin Compact Fluorescent, G24q-1 (2700°K) Z118 18W Double Twin Tube (DTT) 2-Pin

Compact Fluorescent, G24d-2 (2700°K) 7118F 18W Double Twin Tube (DTT) 4-Pin Compact Fluorescent G24g-2 (2700°K) 26W Double Twin Tube (DTT) 4-Pin Z126E Compact Fluorescent, G24q-3 (2700°K) Z126P30 26W Triple Twin Tube (TTT) 4-Pin PL

Compact Fluorescent, GX24q-3 (3000°K) Z132P30 32W Triple Twin Tube (TTT) 4-Pin PL Compact Fluorescent, GX24q-3 (3000°K) Z142P30 42W Triple Twin Tube(TTT) 4-Pin PL Compact Fluorescent, GX24g-4 (3000°K)

Z118TE30 18W Triple Twin Tube(TTT) 4-Pin Compact Fluorescent, GX24q-2 (3000°K) Z126TE30

26W Triple Twin Tube(TTT) 4-Pin Compact Fluorescent, GX24q-3 (3000°K)



### **LAMPS**

#### Description

#### INCANDESCENT

20W T 6 1/2" IF Z7 Z9 40W R16 FL Z10 100W BR25

728 120V GU10 base, line voltage MR16



Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information