



**Product Number:** 69450

**Order Abbreviation:** H33GL-400/DX

**General Description:** 400W, H33, mogul based Mercury lamp, coated, bright white deluxe.

#### Product Information

Abbrev. With Packaging Info.	H33GL400DX 6/CS 1/SKU
ANSI Code 2	H33
Approx. Lumens (initial - vertical)	22000
Approx. Lumens (mean - vertical)	16200
Arc Length (in)	2.8
Arc Length (mm)	71.12
Avg Rated Life (hrs)	24000+
Base	E39 Mogul
Bulb	E120
Diameter (in)	4.606
Diameter (mm)	117.00
Fixture Requirement	O
Hot Restrike Time (min)	3-9
Lamp Finish	Coated
Light Center Length - LCL (in)	7
Light Center Length - LCL (mm)	178
Maximum Base Temperature - Fahrenheit	410
Maximum Base Temperature - Celsius	210
Maximum Bulb Temperature - Fahrenheit	752
Maximum Bulb Temperature - Celsius	400
Maximum Overall Length - MOL (in)	11.5
Maximum Overall Length - MOL (mm)	292
Nominal Wattage (W)	400.00
Operating Position	Universal
Warm-up Time (min)	MAX 15 MINUTES

#### Footnotes

- Mean lumens measured at 50% of average rated life
- In general, Horizontal lumen values will be 5-10% lower than the vertical lumen values.