



Product Number: 69444

Order Abbreviation: H39KB-175

General Description: 175W, H39, mogul based Mercury lamp, clear, blacklight

Product Information

Abbrev. With Packaging Info.	H39KB175 6/CS 1/SKU
ANSI Code 2	H39
Approx. Lumens (initial - vertical)	7700
Approx. Lumens (mean - vertical)	7150
Arc Length (in)	1.8
Arc Length (mm)	45.72
Avg Rated Life (hrs)	24000+
Base	E39 Mogul
Bulb	ED28
Diameter (in)	3.504
Diameter (mm)	89.00
Fixture Requirement	O
Hot Restrike Time (min)	3-9
Lamp Finish	Clear
Light Center Length - LCL (in)	5
Light Center Length - LCL (mm)	127
Maximum Base Temperature - Fahrenheit	410
Maximum Base Temperature - Celsius	210
Maximum Bulb Temperature - Fahrenheit	752
Maximum Bulb Temperature - Celsius	400
Maximum Overall Length - MOL (in)	8.31
Maximum Overall Length - MOL (mm)	211
Nominal Voltage (V)	220.00
Nominal Wattage (W)	175.00
Operating Position	Universal
Warm-up Time (min)	MAX 15 MINUTES

Footnotes

- Mean lumens measured at 50% of average rated life
- In general, Horizontal lumen values will be 5-10% lower than the vertical lumen values.