### HALO<sup>®</sup>

### Description

The Halo H5 series utilizes a 5" aperture designed to accommodate smaller sized PAR20 and PAR30 halogen lamps. The wide variety of trims available allows a number of different lighting effects to be created with one basic housing. The 5" diameter trim size makes the H5RICAT the right choice for applications where dramatic yet inconspicuous lighting is required in an existing ceiling.

Catalog #	Туре
Project	
Comments	Date
Prepared by	

### **Specification Features**

### Housing

- Gasketed die-stamped 20 gauge aluminum.
- Housing will slip through 5 1/2" ceiling opening.
- Integral flange secures fixture against ceiling.
- Housing accommodates a wide range of Halo 5" trims.
- Torsion springs on all trims for quick and easy installation

### **Socket Plate**

- Rigid socket plate adjusts and locks without tools for various lamp sizes
- Socket plate and bracket may be removed when using socket supporting trims

### **Remodel Clips**

 Four remodel clips secure housings and accommodate 1/2" and 5/8" ceiling material

### Slide-N-Side™ Junction Box

Junction box features include:

- Slide-N-Side™ connectors allow non-metallic sheathed cable for both U.S. and Canada to be installed without tools and without removing knockouts
  - Allows wiring connections to be made outside the junction box
  - Simply insert the cable directly into the trap after connections are made
  - Accommodates the following standard non-metallic sheathed cable types: (US) #14/2 , #14/3, #12/2, #12/3 (Canada) #14/2, #14/3, #12/2

## Positioned to accommodate straight conduit runs

- Seven 1/2" trade size conduit knockouts with true pry-out slots
- cULus Listed 26 in 3 box volume
- Listed for through branch (8) No. 12 AWG branch circuit 90° C conductors through the box

### **Quick Connect™**

- Three 4-port push-in "Quick Connect" wire nuts included in junction box
- Speed installation and increase reliability
- · No additional wire nuts required
- · Simply strip and insert supply wires

### Socket

- Porcelain socket with nickel plated brass screw shell
- Snap-in springs secure socket to socket plate, and may be detached when using socket supporting trims
- · Overspray protector included

### **Thermal Protector:**

Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping or misapplied insulation

### Trims:

Halo Fit-All concept offers multiple trim options in a variety of design styles, and functional beam distributions to control beam angle and lumen delivery in accommodating various lamp types including Halogen, CFL and LED

### Compliance

- cULus Listed 1598 luminaire
- · cULus Listed damp location
- cULus Listed for wet location, covered ceiling, with select trims
- · cULus Listed for feed through
- cULus Listed for direct contact with insulation and combustible material\*
- Air-Tite code compliant. Certified under ASTM E283; not exceeding 2.0 cfm (0.944 L/s) air leakage rate tested at a 1.57 psf (75 Pa) pressure differential
- RoHS compliant
- Options to meet Trade Agreements Act requirements

\*Not to be used in direct contact with spray foam insulation (Consult NEMA LSD57-2013)



### **H5RICAT**

5-Inch Insulated Ceiling Air-Tite™ Recessed Remodel Housing

FOR USE IN INSULATED CEILINGS

FOR USE IN EXISTING CEILINGS

# air









### Special Features

Slide-N-Side™ junction box Quick Connect™ push wire nuts Air-Tite™ code compliant

### **Dimensions**







### Ordering Information

Sample Number: H5RICAT 5020SC

Order housing, trim and lamp (by others) separately for a complete luminaire.

Housing

Domestic Preferences(1)

[Blank] = Standard TAA = Trade Agreements Act H5RICAT = 5" IC, Air-Tite, Remodel Housing, 120V

### **Trims**

### Reflectors



5020 PAR Reflector OD: 6-3/8" [162mm]

5020P=White Reflector, White Trim 5020H=Haze Reflector, White Trim 5020SC=Clear Specular Reflector, White Trim

**5020BL**=Black Specular Reflector, White Trim **5020SN**=Satin Nickel Reflector, Satin Nickel Trim **5020TBZ**=Tuscan Bronze Reflector,

Tuscan Bronze Trim



### 5021 Full Reflector

5021-8-1 (162mm)
5021H=Haze Reflector, White Trim
502SC=Clear Specular Reflector, White Trim
5021SN=Satin Nickel Reflector, Satin Nickel Trim 5021TBZ=Tuscan Bronze Reflector,

Tuscan Bronze Trim



## 5107 Specular Reflector, Self-flange OD: 6-5/8" [168mm]

5107SC=Specular Reflector, White Self-flange



### 5120 Full Cone Reflector, Self-flange

OD: 6-5/8" [168mm] **5120WH**=White Reflector, White Self-flange 5120SN=Satin Nickel Reflector, Satin Nickel Self-flange

5120TBZ=Tuscan Bronze Reflector, Tuscan Bronze Self-flange



### 5121 Shallow Full Cone Reflector, Self-flange

OD: 6-5/8" [168mm]

5121WH=White Reflector, White Oversized Self-flange

### **Baffles**



## **5001 PAR Metal Baffle Splay** OD: 6-3/8" [156mm]

5001P=White Baffle, White Trim 5001MB=Black Baffle, White Trim 5001SN=Satin Nickel Baffle, Satin Nickel Trim **5001TBZ**=Tuscan Bronze Baffle, Tuscan Bronze Trim



### 5010 PAR Metal Step Baffle

OD: 6-3/8" [156mm] **5010W**=White Baffle, White Trim

5010=Black Baffle, White Trim



### 5014 Shallow Metal Baffle, Self-flange

OD: 6-5/8" [168mm]

5014P=White Baffle, White Trim 5014MB=Black Baffle, White Trim



# 5016 Coilex® Baffle with Reflector OD: 6-3/8" [162mm] 5016W=White Baffle, White Trim

5016P=Black Baffle, White Trim



### 5102 Tapered Metal Baffle, Self-flange

OD: 6-5/8" [168mm]

5102WB=White Baffle, White Self-flange 5102BB=Black Baffle, White Self-flange



## 5109 Coilex® Tapered Baffle, Self-flange OD: 6-5/8" [168mm]

5109WB=White Plastic Straight Coilex Baffle, White Self-flange

5109BB=Black Plastic Straight Coilex Baffle, White Self-flange 5109BKBB=Black Plastic Straight Coilex Baffle,

Black Self-flange



### <u>5110 Perftex</u>™ <u>Baffle, Self-flange</u>

OD: 6-5/8" [168mm] **5110WB**=White Perftex Baffle, White Self-flange

5110WB=Black Perftex Baffle, White Self-flange 5110BKBB=Black Perftex Baffle,



## 5125 Full Cone Baffle, Self-flanged OD: 6-5/8" [168mm]

5125WB=White Baffle, White Self-flange 5125BB=White Baffle, Black Self-flange 5125BKBB=Black Baffle, Black Self-flange

Black Self-flange



## 5126 Shallow Full Cone Baffle, Self-flanged OD: 6-5/8" [168mm]

5126WB=White Baffle & Self-flanged 5126BB=Black Baffle & White Self-flanged

### Adjustable - Eyeballs & Gimbals



5060 Adjustable Gimbal 20° Tilt, Self-flange OD: 6-3/8" [162mm]

5060P=White Gimbal, White Trim



### <u>5070 Adjustable Eyeball 30° Tilt, Self-flange</u>

OD: 6-3/8" [162mm]

5070P=White Eyeball, White Trim 5070SN=Satin Nickel Eyeball, Satin Nickel Trim 5070TBZ=Tuscan Bronze Eyeball, Tuscan Bronze Trim



### <u>5071 Adjustable Eyeball 30° Tilt, Self-flange</u> OD: 6-1/2" [165mm]

5071P=White Eyeball, White Trim



### 5130 Eyeball 35° Tilt, Self-flange OD: 6-5/8" [168mm]

5130WH=White Eyeball, White Trim



### <u>5135 Eyeball 35° Tilt, Self-flange</u>

OD: 6-5/8" [168mm] 5135WH=White Eyeball, White Trim, Selfflanged



5165 Gimbal 35° Tilt, Self-flange OD: 6-5/8" [168mm] 5165WH=White Gimbal, White Trim

5165BK=Black Gimbal, Black Trim 5165SN=Satin Nickel Gimbal, Satin Nickel Trim 5165TBZ=Tuscan Bronze Gimbal, Tuscan Bronze Trim



### 5222 Regressed Angle Cut Adjustable Gimbal 30° Tilt, Self-flange

OD: 6-5/8" [168mm]

5222WB=White Baffle and Gimbal, White Trim 5222BB=Black Baffle and Gimbal, White Trim 5222SC=Specular Clear Reflector and Gimbal, White Trim

5222H=Haze Reflector and Gimbal, White Trim

### **Lenses & Wet Location Showerlights**



### <u> 5051 Frosted Glass Lens - Showerlight</u>

OD: 6-7/16" [164mm]

5051PS=Frosted Glass Lens, White Trim



### 5054 Frosted Glass Dome Lens - Showerlight

OD: 6-3/8" [162mm]

**5054PS**=Frosted Glass Dome Lens, White Trim **5054SNS**=Frosted Glass Dome Lens, Satin Nickel Trim

5054TBZS=Frosted Glass Dome Lens,



OD: 6-5/8" [168mm]

5150WH=Frost Dome Glass Lens with Reflector, White Plastic Self-flange 5150SN=Frost Dome Glass Lens with Reflector,

Satin Nickel Plastic Self-flange

5150TBZ=Frost Dome Glass Lens with Reflector, Tuscan Bronze Plastic Self-flange



5162WH=Drop Opal Plastic Lens with Reflector, White Plastic Self-flange



5230AH=Frost Glass Lens, Aluminum Haze Squircle Trim

5230PN=Frost Glass Lens, Polished Nickel Squircle Trim
5230SN=Frost Glass Lens, Satin Nickel

Squircle Trim 5230TBZ=Frost Glass Lens, Tuscan Bronze Squircle Trim

# 5255 Soft Square, Frost Curve Glass Lens, Self-flange - Showerlight OD: 7-1/4" [183mm]

5255WH=Frost Curve Glass Lens with Reflector, White Plastic Self-flange

5255SN=Frost Curve Glass Lens with Reflector, Satin Nickel Plastic Self-flange

5255TBZ=Frost Curve Glass Lens with Reflector. Tuscan Bronze Plastic Self-flange

### 5145 Open Wet Location, Shallow Reflector, Self-flange - Showerlight \* OD: 6-5/8" [168mm]

5145WH=White Self-flanged 5145SN=Satin Nickel Self-Flanged 5145TBZ=Tuscan Bronze Self-Flanged Lamp Gasket= (Included)

## 5146 Open Wet Location Full Reflector,

Self-flange - Showerlight \* OD: 6-5/8" [168mm] 5146WH=White Self-flanged 5146SN=Satin Nickel Self-Flanged 5146TBZ=Tuscan Bronze Self-Flanged Lamp Gasket= (Included)

continued

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to <u>DOMESTIC PREFERENCES</u> website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information. \*Outdoor rated lamp only (purchase separately)



### **Ordering Information**

Sample Number: H5RICAT 5020SC

Order housing, trim and lamp (by others) separately for a complete luminaire.

### Domestic Preferences(1)

[Blank] = Standard TAA = Trade Agreements Act

**Trims** 

### Open, Splay & Wall Wash

5000 PAR Metal Splay, Self-flange OD: 6-3/8" [162mm]

5000P=White Splay, White Trim 5000SN=Satin Nickel Splay, Satin Nickel Trim 5000TBZ=Tuscan Bronze Splay, Tuscan Bronze Trim

5175 Open, Self-flange
OD: 6-5/8" [168mm]
5175WH=White Self-flange
5175SN=Satin Nickel Self-flange
5175TBZ=Tuscan Bronze Self-flange

5176 Open, Self-flange OD: 6-5/8" [168mm] 5176WH=White Self-flange 5176SN=Satin Nickel Self-flange 5176TBZ=Tuscan Bronze Self-flange

5185 Open Splay, Self-flange OD: 6-5/8" [168mm] 5185WH=White Self-flange **5185SN**=Satin Nickel Self-flange **5185TBZ**=Tuscan Bronze Self-flange

5186 Open Splay, Self-flange OD: 6-5/8" [168mm]

5186WH=White Self-flange 5186SN=Satin Nickel Self-flange 5186TBZ=Tuscan Bronze Self-flange

### Housing

H5RICAT = 5" IC, Air-Tite, Remodel Housing, 120V

### **Accessory**

### **Oversize Trim Ring**

**OT500P** = Oversized white polymer trim ring for use with 5", 5000 series straight sided trims ONLY. (Not for use with 5100, 5200 or 5300 series trims)

Size: 6" ID x 7-1/4" OD

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to <u>DOMESTIC PREFERENCES</u> website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

\*Outdoor rated lamp only (purchase separately)





