



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

760 Ford St.
80915-0000, CO Colorado Springs
Phone: 719-559-2456
Fax: 719-867-4287



HBL1221GY SP Tog, Ind GRD, 20A 120/277V, Gy *Hubbell Wiring Devices*

Catalog Number	HBL1221GY
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose Ac, Single Pole, 20A 120/277V Ac, Back and Side Wired, Gray Toggle
Weight per unit	0.0770 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Positive Snap
amperage rating	20
connection	Back and Side Wired
Contact Configuration	Two Position
Contact Rating	Per UL 20
Current Rating	20
insulation	False
operating cycles	50,000
pallet quantity	3600
Poles	Single Pole
Switch Type	Toggle
Voltage Rating	120-277
Wattage	5540

Dimensions and Weight

Size	4.06 in x 1.31 in x 1.87 in
------	-----------------------------

Descriptions

Description	SP TOG, IND GRD, 20A 120/277V, GY
extra long description	HWDK HBL1221GY SP TOG, IND GRD, 20A
Long Description	Switches and Lighting Controls, Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired, Gray Toggle
Product Type	SP Tog, Ind GRD, 20A 120/277V, Gy
Special Features	Standard Product

Manufacturer Information

Brand	Hubbell Wiring Devices
GTIN	00783585431369
Manufacturers Part Number	HBL1221GY
series	Extra Heavy Duty
UPC	783585431369



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

760 Ford St.
80915-0000, CO Colorado Springs
Phone: 719-559-2456
Fax: 719-867-4287

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	TOGGLE

Packaging

Carton	1
Package	10
Weight Per each	0.077

Uses, Certifications, and Standards

Application	Back and Side Wired
Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed