# Temporary Power Temporary Industrial Lighting LED Stringer Lights

#### Features

- 90 LEDs for maximum illumination
- · Very low heat output
- Magnetic base included for added hanging flexibility

## **Ordering Information**

**Description** 90 LEDs per fixture, light string with magnetic base included **UPC** 783585528311 Catalog Number HBL182S20LED



HUBBELL

#### Standards

UL CSA ETL

## Specifications

Light Type Plug Type Included LED NEMA 5-15P Magnetic base

## Performance

Electrical	
Lamp Life	50,000 hours
Lumen Output per Fixture	450
Rating	15A 125V
Watt per fixture	6.6
Mechanical	
Cord Length	20 ft.
Number of fixtures	1

#### **Online Resources**

eCatalog



**Wiring Device-Kellems**