# Twist-Lock® Devices 20A, 480V AC, 2 Pole, 3 Wire Grounding Single Flush Receptacle

# HUBBELL

#### **Features**

- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- Face color coding by voltage facilitates locating and mating of proper devices
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

# **Ordering Information**

Description	Device Color	UPC	Catalog Number
Nylon face, back and	Black	783585235691	HBL2340
side wire.			

### Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

#### **Specifications**

Face Nylon

Base Glass-Reinforced thermoplastic polyester (RTP)

Contacts Brass

Terminal Screws #10 - 32 Brass

Mounting Strap Brass

#### **Performance**

**Electrical** 

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

**Environmental** 


Flammability V2 or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)







#### **Accessories**

Plug HBL2341
Wallplate or Weatherproof Cover 1.60" Opening
Switched Enclosure SETL3

## Resources

Customer Use Drawing eCatalog

