Twist-Lock® Devices 20A, 3 Phase 250V AC; 3 Pole, 4 Wire Grounding Insulgrip® Connector

HUBBELL



- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.





Ordering Information

Description Cord Diameter UPC Catalog Number Black and white nylon. 350"-1.150" (9-29) 783585038216 HBL2423

Listings

Listed to UL 498
Fed.Spec. W-C-596
Cortified to CSA C33

Certified to CSA C22.2 No.42

Specifications

Housing / Cord Clamp Nylon


Terminal Retainer Clear polycarbonate

Contacts Brass

Terminal Screws #10-32 Brass (Phillips / Slotted / Robertson)

Terminal Clamp Cold rolled steel – nickel plated

Assembly Screws Steel - nickel plated



Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL94 or CSA 22.2 No. 0.6

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C Minimum -40°C (w/o impact)

Accessories

Plug	HBL2421
Weatherproof Boot	HBL6036
Flanged Inlet	HBL2425
Weatherproof Boot	HBL6035

Resources

Customer Use Drawing eCatalog

