Twist-Lock® Devices 30A, 3 Phase 480V AC, 3 Pole, 4 Wire Grounding

Watertight Safety-Shroud® Flanged Inlet

Features

- UL Type 4X Environmental seal protects connection while in use.
- One-piece, engineered thermoplastic housing is impact-resistant for heavy-duty industrial environments
- Alignment arrows and lock and unlock symbols provide a visual indication that devices are properly connected.
- Closure cap is included for environmental seal when device is not in use
- Catalog number and color-coded voltage rating are easily visible even when in use

Ordering Information

Description Device color UPC Catalog Number Gray PBT housing and Gray 783585231969 HBL2735SW flange

Listings

Listed to UL 498 Fed.Spec. W-C-596

Certified to CSA C22.2 No.42

UL Listed, CSA Certified to Type 4, 4X and Type 12

Specifications

Housing / Flange Gray PBT

Terminal Retainer Clear polycarbonate

Blades Brass

Terminal Screws #10-32 Brass (Phillips / Slotted / Robertson)

Assembly Screws Stainless Steel
Mounting Sscrew Stainless Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental


Flammability V0 per UL94 or CSA 22.2 No.0.17 Moisture Resistance Type 4, 4X, 12, IP66 suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)

HUBBELL







Accessories

Watertight Safety Shroud
Connector
Non-Metallic Backbox
2-Gang Weatherproof Box
HBL2733SW
BB2030N
HBL2030AP

Adapter Plate

HBLZUS

Resources

Customer Use Drawing eCatalog

