#### **IEC Pin and Sleeve**

# 30A, 3 Phase, 480V, 3 Pole, 4 Wire

# Watertight Connector Body

#### **Features**

- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Watertight neoprene glad seal to prevent water ingress from entering at cable entrance
- Sequential contact engagement to prevent a momentary over-voltage
- Market leading UL witnessed HP ratings

# **Ordering Information**

**UPC** Description **Catalog Number** HBL430C7W Watertight IEC Pin and Sleeve 783585404318 Connector Body

#### Listings

UL Listed, File E146033 CSA Certified File LR280C UL Classified to IEC 60309-1 IEC 60309-2

#### **Specifications**

Housing PBT Cord Clamps PBT

Solid Neoprene Glands Covers **PBT** 

Gaskets Santoprene

## **Performance**

**Electrical** 

Certified for current interrupting at full rated **Current Interrupting** 

current

Dielectric Voltage Withstand 3000V AC

Max. Working Voltage 600V RMS

Mechanical

Impact Resistance Per CSA C22.2 No. 182.1 / UL1682

Identification and ratings are a permanent part of **Product Identification** 

the device housing

**Terminal Identification** Terminals identified in accordance with North

American and IEC conventions

**Environmental** 

Moisture Resistance

Flammability V-0

Type 3R, 3RX, 4X and IP68, IP69K Ingress Protection

IEC 60309-1

**Operating Temperatures** Maximum Continuous 75°C; Minimum - 40°C

w/o impact

### **Complementary Products**

Cover Assemblies Cord Clamp and Locking Ring Liquidtight Adapters

#### **Online Resources**

**Customer Sales Drawing** eCatalog

Installation Instructions

# HUBBELL





