# Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding Valise Connector Body

# HUBBELL

#### **Features**

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring
- Insulation displacement terminals reduce assembly time

#### **Ordering Information**

Description UPC Catalog Number Cord Diameter Insulation .230"-.360"(5.8-9.1 783585019680 HBL5963VBK displacement terminals, black nylon

#### Listings

UL Listed to UL498 File E1706 CSA Certified to C22.2 No. 42 File 280C **NEMA® WD-6 Compliant** 

## **Specifications**

Housing Nylon Contacts **Brass** Assembly Screws Plated Steel

## **Performance**

**Electrical** 

**Current Interrupting** Certified for current interrupting at full rated current

Withstands 2,000V minimum Dielectric Voltage

Mechanical

Product Identification Ratings are a permanent part of the device **Terminal Accommodation** #18-16 AWG. Stranded copper wire only.

Terminals identified in accordance with UL 498 and CSA Terminal Identification


**Environmental** 

Flammability UL 94 HB or better

IP Suitability IP20

Maximum continuous 75°C; minimum -40°C (w/o impact) **Operating Temperatures** 







#### Resources

Customer Use Drawing eCatalog

