



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL7810DS 30A 600V 3P Disc SW Shorty *Hubbell Wiring Devices*

Catalog Number	HBL7810DS
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Manual Motor Controllers, Motor Disconnects, Three Pole, 30A 600V Ac, Back and Side Wired Short Toggle
Weight per unit	1.1 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

Features

connection	Pressure Screw Terminals
Current Rating	30
Enclosure Type	None
Item Type	Short Toggle
Material	Stainless Steel
Number of Phases	Three
Poles	3 Pole
Power Rating	18000
terminals	Terminal Screws
Voltage Rating	600

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	30A 600V 3P DISC SW SHORTY
extra long description	HWDK HBL7810DS 30A 600V 3P DISC SW
Long Description	Switches and Lighting Controls, Industrial Grade, Manual Motor Controllers, Motor Disconnects, Three Pole, 30A 600V AC, Back and Side Wired Short Toggle
Product Type	30A 600V 3P Disc SW Shorty
Special Features	Short Toggle

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585202808
Manufacturers Part Number	HBL7810DS
series	Short Toggle
sub brand	Manual Motor Controllers
UPC	783585202808



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Back & Side Wire

Availability

Status Inactive

Packaging

Carton 1

Package 10

Weight Per each 1.1

Uses, Certifications, and Standards

Application Motor Starting w/o Overload Protection

Mounting Screw Mount

standard CSA-C22.2 No.14 Industrial Control File LR-46186;UL 508,
Industrial Control File #E70402

Temperature Rating Minimum Continuous -40 Deg C without Impact