# **Straight Blade Devices**

# 20A, 125V, 2 Pole, 3 Wire Grounding

# **HBL**<sup>®</sup> Extra Heavy Duty MAX Hospital Grade **Duplex Receptacle**

#### **Features**

- · Deep body design with impact resistant face
- Patented ground contact provides redundant grounding
- Unique bypass contact design
- Circuit ID marking area

# **Ordering Information**

Description **Device Color** Deep body design with circuit Red ID face. Back and side wired.

**UPC Number** 783585247533

Catalog Number HBL8300RED

### Listings

UL Listed to UL498 File No. E2186 CSA Certified 22.2, No. 42 File 285 Fed. Spec. W-C-596 **NEMA® WD-6 Compliant** 

#### **Specifications**

PBT Face **PBT** Base

.036". (.9) Nickel plated brass By-Pass Power Contacts


**Ground Contacts** 

Clamping Plate Nickel plated brass **Terminal Screws** Plated brass Mounting Strap Nickel plated brass Automatic Self-grounding Clip Stainless steel Mounting Screws Stainless steel

# HUBBELL







# **Performance**

Dielectric Voltage

**Electrical** 

**Current Interrupting** Certified for current interrupting at full rated

current

Withstands 2,000V minimum

Mechanical

**Product Identification** Ratings are a permanent part of the device #12-#10 AWG stranded or solid copper wire only **Terminal Accommodation Terminal Identification** Terminals identified in accordance with UL 498

and CSA

**Environmental** 

Flammability UI 94 V-0

**Operating Temperatures** Maximum continuous 75°C; minimum -40°C (w/o

impact)

# **Complementary Products**

Wallplate or Weatherproof Cover

**Duplex Opening** 

#### **Online Resources**

**Customer Sales Drawings** eCatalog

Installation Instructions

