



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL9330 RCPT, 2P3W, 30A 250V, 6-30R, BK *Hubbell Wiring Devices*

Catalog Number	HBL9330
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, RTP, Industrial Grade, 2-Pole 3-Wire Grounding, 30A 250V, 6-30R, Black, Single Pack.
Weight per unit	0.4000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	30
connection	Back and Side Wired Screw Terminals
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire Grounding
pallet quantity	2560
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	7,500
Wire Size	#12 to #4

Dimensions and Weight

Size	3.28 in x 2.25 in x 2.23 in
------	-----------------------------

Descriptions

Description	RCPT, 2P3W, 30A 250V, 6-30R, BK
extra long description	HWDK HBL9330 RCPT, 2P3W, 30A 250V,
Long Description	Straight Blade Devices, Receptacles, RTP, Industrial Grade, 2-Pole 3-Wire Grounding, 30A 250V, 6-30R, Black, Single Pack.
Product Type	RCPT, 2P3W, 30A 250V, 6-30R, BK
Special Features	Standard

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015231
Manufacturers Part Number	HBL9330
series	Extra Heavy Duty
UPC	783585015231

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	RECEPTACLE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	6-30R
standard	CSA Certified;NEMA® WD-6 Compliant;UL Listed File E2186