



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1500 West Cotton
75604-0000, TX Longview
Phone: 903-757-8491
Fax: 903-758-0441



HBL9430A RCPT, 3P4W, 30A 125/250V, 14-30R *Hubbell Wiring Devices*

Catalog Number	HBL9430A
Manufacturer	Hubbell Wiring Devices
Description	Designed For Plug-In Ev Charging Applications, Hubbell'S 14-50R Receptacle Is A Premium and Dependable Solution to Exceed The Requirements Of Electric Vehicle Owners. This Receptacle Ensures A Safe and Efficient Charging Experience, Providing Peace Of Mind to Ev Users.
Weight per unit	0.2310 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	30
connection	Back and Side Wired Screw Terminals
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	4-Wire
pallet quantity	1800
Phase	1
Poles	3-Pole
Voltage Rating	125 V;125/250
Wattage	7500
Wire Size	#12 to #4

Dimensions and Weight

Size	3.28 in x 2.75 in x 2.44 in
------	-----------------------------

Descriptions

Description	RCPT, 3P4W, 30A 125/250V, 14-30R
extra long description	HWDK HBL9430A RCPT, 3P4W, 30A 125/2
Long Description	Designed for plug-in EV charging applications, Hubbell's 14-50R receptacle is a premium and dependable solution to exceed the requirements of electric vehicle owners. This receptacle ensures a safe and efficient charging experience, providing peace of mind to EV users.
Product Type	RCPT, 3P4W, 30A 125/250V, 14-30R
Special Features	Standard



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1500 West Cotton
75604-0000, TX Longview
Phone: 903-757-8491
Fax: 903-758-0441

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015293
Manufacturers Part Number	HBL9430A
series	Extra Heavy Duty
UPC	783585015293

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	RECEPTACLE

Packaging

Carton	1
Package	5
Weight Per each	0.231

Uses, Certifications, and Standards

Application	Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	14-30R
standard	Certified to CSA;NEMA® WD-6 Compliant;UL Listed File E2186