ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

HBLDS3AC Disconnect, 30A Unfused, 4X, W/Ac

Hubbell Wiring Devices

Catalog Number	HBLDS3AC
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V Ac, Screw Terminals, Gray, Nema 4XENCLOSURE, With Aux Contact
Weight per unit	2.6 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

Features

action	Snap
actuator	Lever
amperage rating	30
connection	Terminal Screws
Contact Configuration	Two Position
Contact Rating	30A
Current Rating	30
Material	COMPOSITE
operating cycles	6,000 Cycles
pallet quantity	410
Poles	Three Pole
Switch Type	Lever
Voltage Rating	600
Wattage	18000;18000.0000

Dimensions and Weight

Size	8.5 in x 6 in x 4.12 in

Descriptions

Description	DISCONNECT, 30A UNFUSED, 4X, W/AC
extra long description	HWDK HBLDS3AC DISCONNECT, 30A UNFUS
Features	NEC section 430.102(B) requires each motor controller to have a disconnect within line of sight from the motorand driven equipment. Hubbell's Circuit-Lock® Unfused Disconnect Switches are UL listed as a manual motor controller and also "suitable as a motor disconnect" and meet these code requirements.
Long Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA 4XEnclosure, With Aux Contact
Product Type	Disconnect, 30A Unfused, 4X, W/Ac
Special Features	Standard Product with HBLAC1 Aux Contact

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Hubbell Wiring Device-Kellems
GTIN	00783585430607
Manufacturers Part Number	HBLDS3AC
series	Non-Fused
sub brand	Circuit-Lock
UPC	783585430607

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Disconnect Switches

Packaging

Carton	1
Weight Per each	2.6

Uses, Certifications, and Standards

Application	Labelless
Enclosure	Type 4X, IP69k
environmental conditions	NEMA 4X
Frequency Rating	60Hz
Mounting	Mounting Feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
standard	UL Listed