Switched Disconnects and Enclosures

Circuit-Lock® 30A Disconnects with LED Indicators

Suitable as Motor Disconnects

Features

- · Six highly visible integral phase identification LEDs for use on 3 Phase Y system
- LEDs provide secondary means of visual confirmation of make/break on all phases
- Cover cannot be removed with switch in the "ON" position
- Verification of opening of load side contacts
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements

Ordering Information

Description Catalog Number **UPC Number** HBLDS3P Disconnect switch with LEDs, 783585365107 Non Metallic

Listings

cULus Listed

NSF Certified and IP69K Rating

Specifications

Base and Top PBT Handle **PBT** Conduit Hub 3/4 in. Zinc **Enclosure Gasket** Neoprene Galvanized Steel Frame

Stainless Steel 300 Series **Enclosure Screws**

Shaft (Unfused) PBT

Shaft Seal Molded Neoprene

Performance

Dielectric Voltage

Max. Working Voltage

Electrical

Current Interrupting Certified for current interrupting at full rated

current and voltage

Withstands 3000V AC minimum

600V AC RMS

Short Circuit Current Ratings Suitable for use on a circuit capable of delivering (SCCR): (Motor Disconnect) not more than 65kA RMS symmetrical, 600V AC

max. when protected by Class J fuses rated 30A

max.

Mechanical

Impact Resistance In accordance with UL 746C External fully adjustable feet Mounting

Terminal Identification In accordance with UL, CSA and international

conventions

Environmental

Moisture Resistance

Operating Temperature

Flammability UL94-5VA and V0 Classification

Indoor and Outdoor - Type 4X (Wash down, Corrosion resistant); Indoor - Type 12 (Dust-tight, Falling Dirt, Noncorrosive Liquids).


Max. Continous: 75°C: Min. Continuous: -40°C

without impact

UV Resistance All materials are UV stabilized







Complementary Products

Replacement Cover HBLDS3RCP HBL30RGB Replacement Ground Block HBL30RNB Replacement Neutral Block Replacement Switches HBLDS3RS Replacement Mounting Feet HBLRFT1

Online Resources

Customer Use Drawing eCatalog

Installation Instructions

