

Mechanical Interlock Replacement Part Replacement Switch

Ordering Information

Description	UPC	Catalog Number
Replacement switch	783585955179	HBLDS3RS

Product Type
CircuitLock Accessory

Standards

Listed to UL Standard
CSA Certified TYPE 4, 4X and TYPE 12K Enclosure Rating

Performance

Electrical

Current Interrupting	Certified for current interrupting at full rated current voltage
Dielectric Voltage	Withstands 3,000V Min
Max. Working Voltage	600V RMS
Operations	Mechanical 10,000 cycles; Electrical 6,000 cycles

Mechanical

Impact Resistance	In accordance with UL 746C
Mounting	External full adjustable feet
Product Identification	Identification and ratings are part of the external label and receptacle face
Terminal Identification	In accordance with UL, CSA

Environmental

Flammability	Meets UL 94V0 material classification
Moisture Resistance	IP66 suitability
Operating Temperature	Maximum continuous +75°C; Minimum continuous -40°C
UV Resistance	All exposed materials are UV stabilized

Accessories

Enclosure Accommodation	Switched Safety Enclosures, 30A HBLDS Series
-------------------------	---

Online Resources

eCatalog
Installation Instructions

