IEC Pin and Sleeve

Accessories

Replacement Switches

HUBBELL

Ordering Information

DescriptionPin and Sleeve replacement switch block for 60/100A

UPC 783585955216

Catalog Number HBLDS60100RS

Device Color

Gray

Standards

UL Listed CSA Certified

Specifications

Hinge Spring Stainless Steel
Assembly Screws Stainless Steel
Gaskets Neoprene
Interlock Items Replacement Parts



Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstand 3,000V AC Max Working Voltage 600V AC RMS

Mechanical

Impact Resistance In accordance with UL746C

Product Identification Identification and ratings are a part of the external

label and molded into the receptacle mount.
Terminals identified in accordance with North

American and International conventions

Environmental

Terminal Identification

Flammability UL94-5VA and V-0 classification

Ingress Protection IP67 Suitability

Operating Temperatures Max Continuous- 75 $^{\circ}$ C, Minimum -40 $^{\circ}$ w/o Impact

Online Resources

eCatalog

Installation Instructions



