



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HCLR10 10A 600V Class CC Fast Acting Fuse

*Edison Fuses*

Catalog Number	HCLR10
Manufacturer	Edison Fuses
Description	Class CC Fuse, 10 A, 600 V Ac, Melamine (Body);Brass (End Cap) Material, 0.41 In Diameter, 1.50 In Overall Length, 0.02 LB
Weight per unit	0.0200 (lbs/each)
Product Category	Renewable & Non-Renewable

### Features

amperage rating	10
amps	10
class	1.0000 IN X 1.0000 IN X 2.2300 IN
Coil Voltage	Air conditioning disconnect
dimensions	1.0000 IN X 0.4060 IN X 0.4060 IN
Fuse Type	Class CC Fast Acting Fuses
Voltage	600V

### Material, Color, and Finish

Color	0.56 In Diameter X 2.00 In Length
Style	Classroom, Open Office, Private Office, Retail

### Descriptions

Description	10A 600V CLASS CC FAST ACTING FUSE
extra long description	EFSE HCLR10 UL CLASS CC FAST ACTING
Features	Edison offers a complete line of Class CC fuses to meet your circuit and equipment protection needs. These branch circuit rated compact fuses rated 600v, and delivering 200,000a IR Vac Sym provide excellent protection in the smallest package of any UL class of fuses. Choose from our EDCC time-delay fuses for your small horsepower motor circuits, our HCLR fast-acting for your non-inductive lighting and resistance heating loads or our HCTR time-delay fuses for your small control transformer protection.
Special Features	0.032A

### Manufacturer Information

Brand	Eaton
GTIN	00782634420682
sub brand	Full Wattage
UPC	782634420682

### Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.02

## Uses, Certifications, and Standards

Application	Non-Indicating
standard	UL Listed, CSA Certified, RoHS Compliant, CE Marked