



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HCLR3 3A 600V Class CC Fast Acting Fuse

Edison Fuses

Catalog Number	HCLR3
Manufacturer	Edison Fuses
Description	Class CC Fuse, 3 A, 600 V Ac, Melamine (Body);Brass (End Cap) Material, 0.41 In Diameter, 1.50 In Overall Length, 0.02 LB
Weight per unit	0.0300 (lbs/each)
Product Category	Renewable & Non-Renewable

Features

amperage rating	3
amps	3
class	1.0000 IN X 1.0000 IN X 2.2300 IN
Coil Voltage	Air conditioning disconnect
dimensions	1.0000 IN X 0.4060 IN X 0.4060 IN
Fuse Type	Class CC Fast Acting Fuses
Voltage	600V

Material, Color, and Finish

Color	0.56 In Diameter X 2.00 In Length
Style	Education,Government,Healthcare,Hospitality,Manufacturing,Offices & Banks,Religious,Retail

Descriptions

Description	3A 600V CLASS CC FAST ACTING FUSE
extra long description	EFSE HCLR3 UL CLASS CC FAST ACTING
Features	Edison offers a complete line of Class CC fuses to meet your circuit and equipment protection needs. These branch circuit rated compact fuses rated 600v, and delivering 200,000a IR Vac Sym provide excellent protection in the smallest package of any UL class of fuses. Choose from our EDCC time-delay fuses for your small horsepower motor circuits, our HCLR fast-acting for your non-inductive lighting and resistance heating loads or our HCTR time-delay fuses for your small control transformer protection.
Special Features	0.032A

Manufacturer Information

Brand	Eaton
GTIN	00782634420620
sub brand	Full Wattage
UPC	782634420620



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MIDGET FUSES

Type FUSE

Packaging

Carton 1

Package 10

Weight Per each 0.03

Uses, Certifications, and Standards

Application Non-Indicating

standard CSA Certified,UL Listed,RoHS Compliant,CE Marked