

Eaton Edison HCLR fuse

HCLR30

UPC:782634420736

Dimensions:

- **Height:** .406 IN
- **Length:** 1 IN
- **Width:** .406 IN

Weight:.1 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Fast acting, branch circuit
- **Special Features:** Rejection style
- **Application:** Non-inductive loads, lighting and resistance heating circuits
- **Voltage Rating:** 600V
- **Amperage Rating:** 30A
- **Interrupt Rating:** 200 kAIC
- **Class:** Class CC
- **Material Type:** Melamine tube, Nickel-plated brass endcaps
- **Packaging Type:** Standard
- **Quantity:** Carton: 10
- **Fuse Indicator:** Non Indicating

Supporting documents:

- [Product Catalog - Edison](#)

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant