

Eaton HCLR30

Catalog Number: HCLR30

Eaton Edison HCLR fuse, Fast acting branch circuit fuse, Rejection style, Non-inductive loads, Lighting and resistance heating circuits, 30 A, CC, Non-indicating, 200 kAIC, Melamine tube|Nickel-plated brass endcaps, Standard, 10, 600 V

General specifications



Product Name	Catalog Number
Eaton Edison HCLR fuse	HCLR30
UPC	Product Length/Depth
782634420736	1 in
Product Height	Product Width
0.406 in	0.406 in
Product Weight	Warranty
0.1 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

Electrical rating

Amperage Rating

30 A

Interrupt rating

200 kAIC

Voltage rating

600 V

Physical details

Material

Nickel-plated brass endcaps

Melamine tube

Packaging type

Standard

General information

Class

Class CC

Fuse indicator

Non-indicating

Quantity

10

Special features

Rejection style

Resources

Catalogs

[Edison full line catalog 1005](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - HCLR30](#)