



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HF0516414 115V, 35CFM SDMT FLTR Fan *Hoffman Enclosures, Inc.*

Catalog Number	HF0516414
Manufacturer	Hoffman Enclosures, Inc.
Description	HF05 Side-Mount Filter Fan, 115V 35CFM, LT Gray
Weight per unit	2.5 (lbs/each)
Product Category	20180212135018

Features

amperage rating	0.16/0.14 A
flow rate	35 CFM
Material	Plastic
nominal voltage	115
Voltage Rating	115 VAC

Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte
Housing Material	Non-metallic

Dimensions and Weight

Size	6.15 x 6.16 x 3.98 in
------	-----------------------

Descriptions

Description	115V,35CFM SDMT FLTR FAN
extra long description	NVENT HOF HF0516414 IP54 5 in FF 11
Features	HF Side-Mount Filter Fans quickly install into enclosure with a click-fit design; no tools or screws required. Grilles open with the flick of a finger for easy filter replacement.
Long Description	HF05 Side-Mount Filter Fan, 115V 35CFM, Lt Gray
Product Type	IP54 5 In FF 115V 7035

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510341954
Manufacturers Part Number	HF0516414
UPC	783510341954

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	Fans and Filter Fans



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2.4599

Uses, Certifications, and Standards

Application	Power Distribution; Controls and Drives
-------------	---