



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21415 North 15th Lane Suite 116
85027-0000, AZ Phoenix
Phone: 480-681-0668
Fax: 480-681-0669



HF0924414 24V, 70CFM SDMT FLTR Fan

Hoffman Enclosures, Inc.

Catalog Number	HF0924414
Manufacturer	Hoffman Enclosures, Inc.
Description	HF09 Side-Mount Filter Fan, 24V 70CFM, LT Gray
Weight per unit	3.2 (lbs/each)
Product Category	20180212140122

Features

amperage rating	0.35
flow rate	70 CFM
Material	Plastic
nominal voltage	24
Voltage Rating	24 VDC

Material, Color, and Finish

Color	Gray
Color Code	RAL 7035
Finish	Lt Gray;Smooth Matte
Housing Material	Non-metallic

Dimensions and Weight

Size	8.19 x 8.21 x 4.15 in
------	-----------------------

Descriptions

Description	24V,70CFM SDMT FLTR FAN
extra long description	NVENT HOF HF0924414 IP54 9 in FF 24
Features	HF Side-Mount Filter Fans quickly install into enclosure with a click-fit design; no tools or screws required. Grilles open with the flick of a finger for easy filter replacement.
Long Description	HF09 Side-Mount Filter Fan, 24V 70CFM, Lt Gray
Product Type	IP54 9 In FF 24V 7035
Short Description	IP54 9 in FF 24V 7035

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510341978
Manufacturers Part Number	HF0924414
UPC	783510341978

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	Fans and Filter Fans



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21415 North 15th Lane Suite 116
85027-0000, AZ Phoenix
Phone: 480-681-0668
Fax: 480-681-0669

Packaging

Carton	1
Weight Per each	3.18

Uses, Certifications, and Standards

Application	Controls and Drives;Power Distribution
-------------	--