



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton Series C complete molded case circuit breaker

HFD3225

UPC:786679015421

### Dimensions:

- **Height:** 4.13 IN
- **Length:** 3.38 IN
- **Width:** 4.13 IN

**Weight:**4.4 LB

### Warranties:


- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 225A
- **Interrupt Rating:** 100 kAIC at 240 Vac, 65 kAIC at 480 Vac
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600 Vac, 250 Vdc
- **Trip Type:** Fixed thermal, fixed magnetic
- **Circuit Breaker Type:** HFD
- **Circuit Breaker Frame Type:** Complete breaker
- **Frame Size:** F-frame
- **Series:** Series C
- **Terminals:** Load side
- **Frequency Rating:** 50-60 Hz

### Supporting documents:

- [MOEM MCCB Product Selection Guide](#)
- [Eatons Volume 4-Circuit Protection](#)
- [HFD3 3D Inventor](#)
- [HFD3 2D Drawing Xchange](#)
- [F-frame Molded Case Circuit Breaker Drawing](#)



- [HFD3 2D PDF](#)
- [Time Current Curves for Series C® F-Frame Circuit Breakers](#)
- [HFD3 3D Model Xchange](#)
- [Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)
- [Counterfeit and Gray Market Awareness Guide](#)
- [F-Frame 310+ Molded-case circuit breakers 15-225A](#)

**Certifications:**

- UL Listed

**Product compliance:** No Data