



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HJ1210HWPL2LG 11.7X9.7X4.6 N4X FG FLT HC

Hoffman Enclosures, Inc.

Catalog Number	HJ1210HWPL2LG
Manufacturer	Hoffman Enclosures, Inc.
Description	Flat Cover With Latches Type 4X, 11.68X9.69X4.62, LT Gray, Fiberglass
Weight per unit	6.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
Material	Fiberglass

Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte
Style	No Window

Dimensions and Weight

Depth	4.62
Height	11.68
Size	13.30x11.29x5.58 in
Width	9.69

Descriptions

Description	11.7X9.7X4.6 N4X FG FLT HC
extra long description	NVENT HOF HJ1210HWPL2LG Encl Flat C
Features	Enclosures feature a flat, overlapping cover design that ensures a more-secure seal. Available with solid and window covers. Latches provide easy access and security.
Long Description	Flat Cover with Latches Type 4X, 11.68x9.69x4.62, Lt Gray, Fiberglass
Product Type	Encl Flat CVR LTCH FG 12x10x5in
Short Description	TYPE 4X, FLAT HNG LATCH CVR

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510158873
Manufacturers Part Number	HJ1210HWPL2LG
UPC	783510158873

Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 6

Uses, Certifications, and Standards

Application Corrosive Environments; Controls and Drives

nema rating 4X Watertight, corrosion-resistant