



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HJ806HWPL1LG 7.7X5.7X4.1 N4X FG FLT HC

Hoffman Enclosures, Inc.

Catalog Number	HJ806HWPL1LG
Manufacturer	Hoffman Enclosures, Inc.
Description	Flat Cover With Latches Type 4X, 7.71X5.72X4.05, LT Gray, Fiberglass
Weight per unit	4.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
Material	Fiberglass

Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte
Style	No Window

Dimensions and Weight

Depth	4.05
Height	7.71
Size	9.30x7.31x4.98 in
Width	5.72

Descriptions

Description	7.7X5.7X4.1 N4X FG FLT HC
extra long description	NVENT HOF HJ806HWPL1LG TYPE 4X, FLA
Features	Enclosures feature a flat, overlapping cover design that ensures a more-secure seal. Available with solid and window covers. Latches provide easy access and security.
Long Description	Flat Cover with Latches Type 4X, 7.71x5.72x4.05, Lt Gray, Fiberglass
Product Type	Type 4X, Flat HNG Latch CVR
Short Description	TYPE 4X, FLAT HNG LATCH CVR

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510158859
Manufacturers Part Number	HJ806HWPL1LG
UPC	783510158859

Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status.....Inactive.....

Packaging

Carton.....1.....

Weight Per each.....4.....

Uses, Certifications, and Standards

Application.....Corrosive Environments, Controls and Drives.....

nema rating.....4X Watertight, corrosion-resistant.....