

Eaton HKD3400

Catalog Number: HKD3400

Eaton Series C complete molded case circuit breaker, K-frame, HKD, Fixed thermal, Fixed magnetic trip, Three-pole, 400 A, 600 Vac, 250 Vdc, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, Aluminum, Line and load, 50/60 Hz



General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	HKD3400
	UPC
	786679319420
Product Length/Depth	Product Height
4.1 in	5.5 in
Product Width	Product Weight
5.5 in	11.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

400 A

Voltage rating

600 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

HKD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Line and load

Frame

K

Frequency rating

50 to 60 Hz

Terminal material

Aluminum

Interrupt rating

65 kAIC at 480 Vac

100 kAIC at 240 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[StrandAble terminals product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Multi-wire lugs product aid](#)

[Motor protection circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[310+ MCCB product family pocket folder](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[K-Frame 310+ Molded-case circuit breakers](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[HKD3 2D PDF](#)

[HKD3 3D Inventor](#)

[HKD3 3D Model Xchange](#)

[HKD3 AutoCAD 2D Footprint \(mm\)](#)

[HKD3 2D Drawing Xchange](#)

[HKD3 AutoCAD 2D Footprint](#)

Installation instructions

[Instruction Leaflet for the KES 310+ Electronic Trip Unit](#)

[Installation Instructions for DK, KDB, KD, HKD, KDC, KW, HKW, KWC, CKD, CHKD Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit breakers explained](#)

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - HKD3400](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

MOEM MCCB product selection guide

Series C J-Frame molded case circuit breakers time current curves

F-Frame 310+ Molded-case circuit breakers 15-225A

Series C F-Frame molded case circuit breakers



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)