



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLC6099301EWH12X *Delisted*6" 15W Led Disk Light 3K 90CRI 120V 900L *Cooper Lighting Solutions*

Catalog Number	HLC6099301EWH12X
Manufacturer	Cooper Lighting Solutions
Description	6" Led Surface Light, 900 Lumens, 90 Cri, 3000K CCT, 120V, Matte White, Qty 12 Bulk Pack
Weight per unit	0.7300 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.133
dimmable	Yes
Efficiency	58.8 LpW
Lamp Type	LED
lumens	925
Mounting Location	Damp location listed
Socket Type	N/A
Voltage Rating	120V
Wattage	15.7

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	6" LED SURFACE LIGHT 90 CRI 3000K 120V Dimmable WHITE 12PK
extra long description	ETNCL HLC6099301EWH-12BP HLC, 6IN,
Long Description	6" LED surface light, 900 lumens, 90 CRI, 3000K CCT, 120V, matte white, Qty 12 bulk pack
Product Type	HLC, 6IN, 900LM, 3000K, 12 Bulk BLK PK
Special Features	Low-profile lens surface-mount luminaire, Ceiling/wall mounting

Manufacturer Information

Brand	Cooper Lighting Solutions
GTIN	00080083884728
Manufacturers Part Number	HLC6099301EWH-12BP
UPC	080083884728

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	HLC LED



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	12
Weight Per each	0.73

Uses, Certifications, and Standards

Application	lighting
Mounting	Ceiling;Surface