

0

HALO[®]

HLC Series Surface LED Downlight







halolighting.com

HALO[®] HLC Series

The HALO HLC is a low profile, high performance surface mount luminaire that offers a slim profile and below the ceiling installation, with no plates or clips.

9″

with motion sensor


halolighting.com


halolighting.com

4″

6**″**

97





- 4" low profile surface mounting luminaire
- 800 lumen package is available with 3 dedicated CCT -3000K, 4000K, 5000K
- 11.2W, Integral 120V 60 Hz constant current driver
- 90 CRI minimum as standard
- L70 @ 50,000 Hrs
- Dimmable to 10% with many 120V leading-edge and trailing-edge phase control dimmers
- Five-year limited warranty
- Installs in many 3-1/2" and 4" ceiling junction boxes as well as pancake boxes
- UL Certified for US and Canada
- UL Damp Location Listed for walls & ceiling
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements

Energy Data				
753 @ 3000K		Inrush (A)	.106 (A)	
120V	1	THD	≤ 29%	
.106 (mA)]	PF	≥ 0.90	
12.6 (W)]	T Ambient	-30° - +40°C	
60 (LPW)]	Sound Rating	≤ 22dba	
	753 @ 3000K 120V .106 (mA) 12.6 (W)	753 @ 3000K 120V .106 (mA) 12.6 (W)	753 @ 3000K Inrush (A) 120V THD .106 (mA) PF 12.6 (W) T Ambient	



Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Appliance Efficiency Database under JA8.




Ordering Information

SAMPLE NUMBER: HLC4079301EWH-6BP

Models	Lumens	CRI / CCT
HLC4 = 4-inch LED surface light	07 = 750 lumen (nominal)	930=90 CRI minimum, 3000K CCT 940=90 CRI minimum, 4000K CCT 950=90 CRI minimum, 5000K CCT
Driver	Finish	Packaging
1E = 120V 60Hz, LE & TE phase cut 10% dimming	WH = matte white	-6BP = Qty 6 bulk pack (not for individual sale) -12BP = Qty 12 bulk pack

1. 3000K only (12 bulk pack)





- 6" low profile surface mounting luminaire
- 900 lumen package is available with 3 dedicated CCT -3000K, 4000K, 5000K
- 11.2W, Integral 120V 60 Hz constant current driver
- 90 CRI minimum as standard
- L70 @ 50,000 Hrs
- Dimmable to 10% with many 120V leading-edge and trailing-edge phase control dimmers
- Five-year limited warranty
- Installs in many 3-1/2" and 4" ceiling junction boxes as well as pancake boxes
- UL Certified for US and Canada
- UL Damp Location Listed for walls & ceiling
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements

Ordering Information

SAMPLE NUMBER: HLC6099301EWH-6BP

Models	Lumens	CRI / CCT
HLC6 = 6-inch LED surface light	09 = 900 lumen (nominal)	930=90 CRI minimum, 3000K CCT 940=90 CRI minimum, 4000K CCT 950=90 CRI minimum, 5000K CCT
Driver	Finish	Packaging

1. 3000K only (12 bulk pack)

Energy Data				
Lumens	925 @ 3000K		Inrush (A)	.133 (A)
Input Voltage	120V		THD	≤ 29%
Input Current	.133 (mA)		PF	≥ 0.90
Input Power	15.7 (W)		T Ambient	-30° - +40°C
Efficiency	58.8 (LPW)		Sound Rating	≤ 22dba



Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements.




Certified to California Appliance Efficiency Database under JA8.






HLC9




HLCMS9



Motion Sensor Benefits:

- Convenience / Safety lights come on as you enter the space
- Energy saving reduces the amount of energy used
- Cost savings reduces energy consumption
- Sleek design



Energy Data				
Lumens	1230		Inrush (A)	2.1 A @ 14 mS
Input Voltage	120V		THD	≤ 20%
Input Current	.132 (mA)		PF	≥ 0.90
Input Power	17.6 (W)		T Ambient	-30° - +40°C
Efficiency	69.9 (LPW)]	Sound Rating	≤ 22dba



Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Appliance Efficiency Database under JA8.



halolighting.com

HLCMS9

- 9" low profile surface mounting luminaire
- 1200 lumen package is available with 2 dedicated CCT -3000K, 4000K
- 17.6W, Integral 120V 60 Hz constant current driver
- 90 CRI minimum as standard
- L70 @ 50,000 Hrs
- Dimmable to 10% with many 120V leading-edge and trailing-edge phase control dimmers
- Five-year limited warranty
- Installs in many 3-1/2" and 4" ceiling junction boxes as well as pancake boxes
- UL Certified for US and Canada
- UL Damp Location Listed for walls & ceiling
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements

Ordering Information

SAMPLE NUMBER: HLC9129301EWH

Models	Lumens	CRI / CCT			
HLC9 = 9-inch LED surface light HLCMS9 = 9-inch LED surface light with Motion Sensor	12 = 1200 lumen (nominal)	930=90 CRI minimum, 3000K CCT 940=90 CRI minimum, 4000K CCT			
Driver		Finish			
1E = 120V 60Hz, LE & TE phase cut 10% dimming		WH = matte white			

Compatible Junction Boxes*

Lighting Control Solution

Octagon steel light fixture / fan box	Square steel deep box
4" x 4" x 2-1/8"	4" x 4" x 1-1/2"
Round new work fixture box (plastic)	Round new work ceiling box (plastic)
4" diameter x 2-3/16"	3-1/2" diameter x 2-3/4"
Round old work fixture box (plastic) 4" diameter x 2-3/16"	Round new work fixture box (plastic) with bar hanger 4″ diameter x 2-3/16″
	4 diameter x 2-3/16
Round surface mount	Round ceiling pan
4" diameter x 1-1/2"	4" diameter x 13/16"
TP316 Eaton's Crouse-Hinds junction box for non-metallic cable 4" x 2-1/8"	TP317 Eaton's Crouse-Hinds junction box for metal clad cable 4" x 2-1/8"

*This is a representative list of compatible junction boxes only. Information contained in this literature about other manufacturers' products is from published information made available by the manufacturer and is deemed to be reliable, but has not been verified. Eaton makes no specific recommendation on product selection and there are no warranties of performance or compatibility implied. Installer must determine that site conditions are suitable to allow proper installation of the mounting bracket in the box.

HALOHOME



HALO Home In-wall Smart Dimmer

HIWMA1BLE40AWH Controls standard lighting fixtures with dimmer or HALO Home mobile app. Features include: • ON/OFF

- Dim
- Group
- SceneSchedule



Product and Photometric Data

HLC4079301EWH-6BP

	ССТ	Lumens	Power (W)	LPW
	3000K	753	12.6	60
HLC4	4000K	761	12.3	62
	5000K	874	12.5	69.9

HLC4079301EWH-6BP - 3000K				
Luminaire	Luminaire lumens			
Input watts		12.6		
LER (LF	LER (LPW)			
Creating	0-180	1.28		
Criteria	Spacing Oritoria 90-270			
Ontenia	Diagonal	1.4		
Beam angle	degrees)	115.1		
Field angle (Field angle (degrees) 170			

Zonal lumen	Lumens	% Lumens		
0-30	191	25.4		
0-40	314	41.7		
0-60	562	74.6		
0-90	744	98.8		

Color Metric Summary					
3000K 4000K 5000K					
TM-30-15	Rf = 87	Rf = 87	Rf = 87		
1101-30-15	Rg = 95	Rg = 95	Rg = 95		
CRI/CIE	Ra = 91	Ra = 91	Ra = 91		
CNI/CIE	R9 = 60	R9 = 60	R9 = 60		


CCT - Range of 3000K- 5000K

Product and Photometric Data

HLC6099301EWH-6BP

	ССТ	Lumens	Power (W)	LPW
	3000K	925	15.7	58.8
HLC6	4000K	939	15.7	59.8
	5000K	1048	15.7	66.8


HLC6099301	EWH-6BP	- 3000K	E
Luminaire	lumens	925	
Input watts		15.7	
LER (LPW)		59	
. ·	0-180	1.28	
Spacing Criteria	90-270	1.28	
Criteria	Diagonal	1.4	
Beam angle (degrees)		114.4	
Field angle (degrees)		166	



	Color Metr	ic Summar	у	CCT - Range	of 3000K- 5000K
	3000K	4000K	5000K	warm	cool
TM-30-15	Rf = 87	Rf = 88	Rf = 90		
1101-30-15	Rg = 95	Rg = 96	Rg = 97		
CRI/CIE	Ra = 92	Ra = 92	Ra = 92		
CNI/CIE	R9 = 60	R9 = 66	R9 = 62	1	14°




HLC9129301EWH




Spacing criterion:	(0-180) 1.27
	(90-270) 1.27
	(Diagonal) 1.4
Beam Angle: 115	
Lumens: 1255	
Input Watts: 17.41	W
Efficacy: 72.1 LPW	1
Test Report: HLC9129301EWH	IES

Zonal Lumen	Lumens	% Lumens
0-30	312	24.9
0-40	514	41
0-60	921	73.4
0-90	1227	97.8





HLCMS9129301EWH



Spacing criterion: (0-180) 1.27 (90-270) 1.27 (Diagonal) 1.39 Beam Angle: 115° Lumens: 1285 Input Watts: 17.24 W Efficacy: 74.6 LPW Test Report: HLCMS9129301EWH.IES

Zonal Lumen	Lumens	% Lumens
0-30	320	24.9
0-40	526	40.9
0-60	941	73.2
0-90	1256	97.7

TM-30-15	Rf = 94	
	Rg = 98	
CRI/CIE	Ra = 94.6	
	R9 = 58.4	
CCT - Range of 3000K- 4000K		
warm cool		

Cooper Lighting Solutions

1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

Canada Sales 5925 McLaughlin Road Mississauga, Ontario L5R 1B8 P: 905-501-3000 F: 905-501-3172

Our Lighting Product Lines

Ametrix AtLite Corelite Ephesus Fail-Safe HALO HALO Commercial Invue io IRiS Lumark Lumière McGraw-Edison Metalux MWS Neo-Rav Portfolio RSA Shaper Streetworks Sure-Lites

Our Controls Product Lines

Fifth Light Technology Greengate iLight (International Only) iLumin Zero 88

Connected Lighting Systems

Distributed Low-Voltage Power HALO Home iLumin Plus LumaWatt Pro WaveLinx

© 2020 Cooper Lighting Solutions All Rights Reserved Printed in USA Publication No. BR518094EN May 2020

Products, specifications and compliances are subject to change without notice.

Cooper Lighting Solutions is a registered trademark. All other trademarks are property of their respective owners.

