



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLR2A 10A 300V Inline Fuse Holder

Bussmann Fuses

Catalog Number	HLR2A
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series, Fuse Holder, 300V, 15A, 18 Awg (Solid Copper) 6 In Black Insulated Line/Load Side Wire, Panel, For Use With In-Line Non-Rejecting GLR Fuse, Non Indicating
Weight per unit	0.3400 (lbs/each)
Product Category	20260323114948

Features

amperage rating	15 A
connection	18 AWG (solid copper) 6 in black insulated line/load side wire
dimensions	0.8500 IN X 0.8500 IN X 7.5500 IN
Voltage Rating	300 V

Dimensions and Weight

Size	0.850 In Diameter X 2.250 In Length
------	-------------------------------------

Descriptions

Description	10A 300V INLINE FUSE HOLDER
extra long description	EFSE HLR-2A BUSS FUSEHOLDER
Long Description	Eaton Bussmann series, fuse holder, 300v, 15a, 18 awg (solid copper) 6 in black insulated line/load side wire, panel, for use with in-line non-rejecting glr fuse, non indicating
Product Type	Buss Fuseholder
Special Features	For Use With In-Line Non-Rejecting GLR Fuse

Manufacturer Information

Brand	Eaton
GTIN	00051712567466
Manufacturers Part Number	HLR-2A
UPC	051712567466

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Non Rejecting

Packaging

Carton	1
Weight Per each	0.34



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Robotics
Mounting	PANEL
standard	RoHS Compliant,Contact factory