



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLS6099301EWH12B 6" 15W Led Disk Light 30K 90CRI 120V 900LM 6 Pack *Cooper Lighting Solutions*

| | |
|------------------|--|
| Catalog Number | HLS6099301EWH12B |
| Manufacturer | Cooper Lighting Solutions |
| Description | 6" Led Surface Light, 900 Lumens (Nominal), 90 Cri Minimum, 3000K CCT, 120V 60HZ, Le and Te Phase, Matte White Flange Cut 10 Percent Dimming, Qty 12 Bulk Pack (Not For Individual Sale) |
| Weight per unit | 7.6 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|--------|
| amperage rating | 0.128A |
| Lamp Type | LED |
| Voltage Rating | 120V |
| Wattage | 15.4 W |

Material, Color, and Finish

| | |
|--------|-------------|
| Finish | Matte White |
| Style | (blank) |

Descriptions

| | |
|------------------------|--|
| extra long description | CLS HLS6099301EWH-12BP HLS, 6IN, 90 |
| Long Description | 6" LED surface light, 900 lumens (nominal), 90 CRI minimum, 3000K CCT, 120V 60Hz, LE and TE phase, matte white flange cut 10 percent dimming, Qty 12 bulk pack (not for individual sale) |
| Product Type | HLS, 6IN, 900LM, 3000K, Wet, 12PK |
| Special Features | Sizes include 4", 6", & 9" |

Manufacturer Information

| | |
|---------------------------|--------------------|
| Brand | HALO |
| GTIN | 00080083256846 |
| Manufacturers Part Number | HLS6099301EWH-12BP |
| UPC | 080083256846 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type | HLS Round LED Surface Mount |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 7.56 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | lighting |
| Mounting | Surface Mount |
| standard | Energy Star;IECC Compliant;UL Listed;Title 24 Compliant;RoHS Compliant |