Eaton HP402442

Catalog Number: HP402442

Eaton house panel, 400A, Aluminum, No bypass, NEMA 3R, Underground, 22 kAIC, Lug landings for compression, lugs not included, DK2400, Surface mounting, C:42, S:1, SP:24, None, Ring, Type BR breakers, 120/240V, 4306, Single-phase



General specifications

Product Name Eaton house panel UPC 786676000567 Product Height 44 in Product Weight

120 lb

Product Length/Depth 6 in Product Width 29.75 in Warranty Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances EUSERC Approved Certifications UL Listed

Catalog Number HP402442



defaultTaxonomyAttributeLabel

Туре

House panel

Interrupt rating

10 kAIC

Enclosure

NEMA 3R

Secondary circuit breaker

None

Amperage Rating

400 A

Line

Lug landings for compression, lugs not included

Mounting

Surface

Number of spaces

24

Security

Ring

Voltage rating

120/240 V

Number of sockets

1

Used with

Type BR breakers

Bypass

None

Number of circuits

42

Bus material

Aluminum

Feed type

Bottom

Main circuit breaker

DK2400

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings Dimensional Drawing

Specifications and datasheets

Technical Data Residential Meter Breakers: Type CH and BR Residential

Eaton Specification Sheet - HP402442



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia