

Eaton HP816P400BSL

Catalog Number: HP816P400BSL

Eaton house panel, 400A, Aluminum, Lever bypass, NEMA 3R, Overhead/Underground, 22 kAIC, Lug landings for compression, lugs not included, CSR2200, Surface mount, C:16, S:1, SP:8, BW/BWH, Ring, Type BR breakers, 120/240V, 4306, 1 PH



General specifications

Product Name

Eaton house panel

Catalog Number

HP816P400BSL

UPC

782116080250

Product Length/Depth

6 in

Product Height

44 in

Product Width

29.75 in

Product Weight

160 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

EUSERC Approved

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

House panel

Interrupt rating

10 kAIC

22 kAIC

Enclosure

NEMA 3R

Secondary circuit breaker

BW/BWH

Amperage Rating

400 A

Line

Lug landings for compression, lugs not included

Mounting

Surface

Number of spaces

8

Security

Ringless

Voltage rating

120/240 V

Number of sockets

1

Used with

Type BR breakers

Bypass

Lever

Number of circuits

16

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR2150

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER BREAKER HP816P400BSL(BL)

Specifications and datasheets

Eaton Specification Sheet - HP816P400BSL



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)