

Eaton HP816P400BSLBL

Catalog Number: HP816P400BSLBL

Eaton house panel, 400A, Aluminum, Lever bypass, NEMA 3R, Overhead/Underground, 22 kAIC, Lug landings for compression, lugs not included, CSR2200, Surface mounting, C:16, S:1, SP:8, BW/BWH, Ring, Type BR breakers, 120/240V, 4306



Photo is representative

General specifications

Product Name

Eaton house panel

UPC

786685970950

Product Height

44 in

Product Weight

160 lb

Catalog Number

HP816P400BSLBL

Product Length/Depth

6 in

Product Width

29.75 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

EUSERC Approved

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

House panel

Interrupt rating

10 kAIC

22 kAIC

Enclosure

NEMA 3R

Secondary circuit breaker

BW/BWH

Amperage Rating

400 A

Line

Lug landings for compression, lugs not included

Mounting

Surface

Number of spaces

8

Security

Ring

Voltage rating

120/240 V

Number of sockets

1

Used with

Type BR breakers

Bypass

Lever

Number of circuits

16

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR2150

Resources

Specifications and datasheets

Eaton Specification Sheet - HP816P400BSLBL



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)