



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HR100DX38 100W ED23.5 Mercury Vapor White Mogul Base Lamp

Ge By Current Lamps

Catalog Number	HR100DX38
Manufacturer	Ge By Current Lamps
Description	Ge Mercury ED23.5
Weight per unit	0.3800 (lbs/each)
Product Category	Hid Mercury Vapor Lamps

Features

average life	20000
Base	E39
lumens	4000.0;4000.0000
Wattage	100

Material, Color, and Finish

Color	Delux white
color rendering index (cri)	50.0
color temperature	3900
Finish	Delux white
Style	Open or enclosed fixtures

Descriptions

Description	100W ED23.5 MERCURY VAPOR WHITE MOGUL BASE LAMP
extra long description	GEL HR100DX38 22575 MERCURY
Long Description	GE Mercury ED23.5
Product Type	22575 Mercury
Special Features	7.5IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168225755
Manufacturers Part Number	HR100DX38
UPC	043168225755

Taxonomies, Classifications, and Categories

Category Description	MERCURY VAPOR
----------------------	---------------

Packaging

Carton	1
Package	12
Weight Per each	0.38

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------