



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HR175A39 *Delisted* 175W ED28 Mercury Vapor Clear Mog Base

Ge By Current Lamps

Catalog Number	HR175A39
Manufacturer	Ge By Current Lamps
Description	Ge, 24048, 175 WTT, 7850 LM, 5700 KV, 15 Cri, Mogul Screw (E39) Base, 20000 HR Average Life
Weight per unit	0.5200 (lbs/each)
Product Category	Hid Mercury Vapor Lamps

Features

average life	20000.0
Base	E39
lumens	7850.0
Wattage	175.0

Material, Color, and Finish

Color	Colorless
color rendering index (cri)	15.0
color temperature	5700.0
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	*DELISTED* 175W ED28 MERCURY VAPOR CLEAR MOG BASE
extra long description	GEL HR175A39 24048 MERCURY
Long Description	GE, 24048, 175 WTT, 7850 LM, 5700 KV, 15 CRI, Mogul Screw (E39) Base, 20000 HR Average Life
Product Type	24048 Mercury
Special Features	8.25IN Length

Manufacturer Information

Brand	GE Current
GTIN	00043168240482
Manufacturers Part Number	HR175A39
UPC	043168240482

Taxonomies, Classifications, and Categories

Category Description	MERCURY VAPOR
----------------------	---------------

Packaging

Carton	1
Package	12
Weight Per each	0.52



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Universal burning position