



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

760 Ford St.
80915-0000, CO Colorado Springs
Phone: 719-559-2456
Fax: 719-867-4287



HR250DX37 250W ED28 Mercury Vapor White Mogul Base Lamp

Ge By Current Lamps

Catalog Number	HR250DX37
Manufacturer	Ge By Current Lamps
Description	Ge, 32127, 250 WTT, 11200 LM, 3900 KV, 50 Cri, Mogul Screw (E39) Base, 20000 HR Average Life
Weight per unit	0.4500 (lbs/each)
Product Category	Hid Mercury Vapor Lamps

Features

average life	20000.0
Base	E39
lumens	11200.0
Wattage	250.0

Material, Color, and Finish

Color	Delux white
color rendering index (cri)	50.0
color temperature	3900.0
Finish	Delux white
Style	Open or enclosed fixtures

Descriptions

Description	250W ED28 MERCURY VAPOR WHITE MOGUL BASE LAMP
extra long description	GEL HR250DX37 32127 MERCURY
Long Description	GE, 32127, 250 WTT, 11200 LM, 3900 KV, 50 CRI, Mogul Screw (E39) Base, 20000 HR Average Life
Product Type	32127 Mercury
Special Features	8.25IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168321273
Manufacturers Part Number	HR250DX37
UPC	043168321273

Taxonomies, Classifications, and Categories

Category Description	MERCURY VAPOR
----------------------	---------------

Packaging

Carton	1
Package	12
Weight Per each	0.45

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------