



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HR400DX33 400W ED37 Mercury Vapor White Mogul Base Lamp

Ge By Current Lamps

| | |
|------------------|--|
| Catalog Number | HR400DX33 |
| Manufacturer | Ge By Current Lamps |
| Description | Ge, 23998, 400 WTT, 22600 LM, 3900 KV, 50 Cri, Mogul Screw (E39) Base, 20000 HR Average Life |
| Weight per unit | 0.8100 (lbs/each) |
| Product Category | Hid Mercury Vapor Lamps |

Features

| | |
|--------------|---------|
| average life | 20000.0 |
| Base | E39 |
| lumens | 22600.0 |
| Wattage | 400.0 |

Material, Color, and Finish

| | |
|-----------------------------|---------------------------|
| Color | Delux white |
| color rendering index (cri) | 50.0 |
| color temperature | 3900.0 |
| Finish | Delux white |
| Style | Open or enclosed fixtures |

Descriptions

| | |
|------------------------|--|
| Description | 400W ED37 MERCURY VAPOR WHITE MOGUL BASE LAMP |
| extra long description | GEL HR400DX33 23998 MERCURY |
| Long Description | GE, 23998, 400 WTT, 22600 LM, 3900 KV, 50 CRI, Mogul Screw (E39) Base, 20000 HR Average Life |
| Product Type | 23998 Mercury |
| Special Features | 11.31IN Length |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168239981 |
| Manufacturers Part Number | HR400DX33 |
| UPC | 043168239981 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | MERCURY VAPOR |
|----------------------|---------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.81 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|