



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3315 Park Place
75462-0000, TX Paris
Phone: 903-784-1916
Fax: 903-784-0107



HR400DX33 *Delisted* 400W ED37 Mercury Vapor White Mog Base *Ge By Current Lamps*

Catalog Number	HR400DX33
Manufacturer	Ge By Current Lamps
Description	Ge, 23998, 400 WTT, 22600 LM, 3900 KV, 50 Cri, Mogul Screw (E39) Base, 20000 HR Average Life
Weight per unit	0.8100 (lbs/each)
Product Category	Hid Mercury Vapor Lamps

Features

average life	20000.0
Base	E39
lumens	22600.0
Wattage	400.0

Material, Color, and Finish

Color	Delux white
color rendering index (cri)	50.0
color temperature	3900.0
Finish	Delux white
Style	Open or enclosed fixtures

Descriptions

Description	*DELISTED* 400W ED37 MERCURY VAPOR WHITE MOG BASE
extra long description	GEL HR400DX33 23998 MERCURY
Long Description	GE, 23998, 400 WTT, 22600 LM, 3900 KV, 50 CRI, Mogul Screw (E39) Base, 20000 HR Average Life
Product Type	23998 Mercury
Special Features	11.31IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168239981
Manufacturers Part Number	HR400DX33
UPC	043168239981

Taxonomies, Classifications, and Categories

Category Description	MERCURY VAPOR
----------------------	---------------

Packaging

Carton	1
Package	6
Weight Per each	0.81

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------