



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1135 Butler Road  
77573-0000, TX League City  
Phone: 281-833-5333  
Fax: 281-833-5334



## HSTT38CC .37"X100' CLR Thin Wall HS Panduit Corporation

|                  |  |
|------------------|--|
| Catalog Number   | HSTT38CC   |
| Manufacturer     | Panduit Corporation  |
| Description      | Thin Wall Heat Shrink, .38" (9.5MM) Diameter, Clear Cross-Linked Polyolefin, 100 FT. (30.5M) Per Reel. |
| Weight per unit  | 0.9500 (lbs/each)  |
| Product Category | Insulating Materials   |

### Features

|                  |      |
|------------------|------|
| flammability     | N/A  |
| media            | Yes  |
| outside diameter | 0.37 |
| Shrink Ratio     | 2:1  |

### Material, Color, and Finish

|       |           |
|-------|-----------|
| Color | Colorless |
|-------|-----------|

### Dimensions and Weight

|           |       |
|-----------|-------|
| Thickness | 0.025 |
|-----------|-------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | .37"X100' CLR THIN WALL HS   |
| extra long description | PAN HSTT38-CC Dry-Shrink™ HSTT38-CC  |
| Long Description       | Thin wall heat shrink, .38" (9.5mm) diameter, clear cross-linked polyolefin, 100 ft. (30.5m) per reel. |
| Product Type           | Dry-Shrink™ HSTT38-CC Heat Shrink  |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Panduit®       |
| GTIN                      | 00074983747191 |
| Manufacturers Part Number | HSTT38-CC      |
| UPC                       | 074983747191   |

### Taxonomies, Classifications, and Categories

|      |             |
|------|-------------|
| Type | Heat-Shrink |
|------|-------------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per roll | 0.95 |

### Uses, Certifications, and Standards

|             |                                       |
|-------------|---------------------------------------|
| Application | For Dry Locations                     |
| standard    | UL Recognized, CSA Approved, MIL SPEC |