



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC1 4" Incandescent Ic Recess

Lithonia Lighting

Catalog Number	IC1
Manufacturer	Lithonia Lighting
Description	
Weight per unit	3.0 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

aperture size	4-in
Fixture Type	Incandescent Line Voltage
Lamp Type	Incandescent Line Voltage
Lamp Wattage	50 WTT
Number of Lamps	1 PH
Shape	Round IN
Voltage Rating	ELBOW FITTING, 316 STAINLESS STEEL MATERIAL; 1/2 INCH SIZE A; 1/2 INCH SIZE B; .5 SIZE A - DECIMAL; .5 SIZE B - DECIMAL; 1/2 SIZE A - FRACTIONAL; 1/2 SIZE B - FRACTIONAL; NUCLEAR, PHARMACEUTICAL INDUSTRY CHEMICAL, PETROCHEMICAL APPLICATION; CAST PROCESS

Descriptions

Description	4" INCANDESCENT IC RECESS
Product Type	4IN Ic HSG

Manufacturer Information

Brand	JUNO
GTIN	00661209700001
sub brand	Juno
UPC	661209700001

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	Downlight; Adjustable

Packaging

Carton	1
Weight Per each	3

Uses, Certifications, and Standards

Application	Recessed Residential
-------------	----------------------



Description

IC rated, energy efficient Air-Loc® sealed double wall construction housing does not require separate Air-Loc gasket • Can be completely covered with insulation • Air-Loc housing with all trims stops infiltration and exfiltration of air, reducing heating and cooling costs

Listings

UL Listed, C-UL/CSA certified for through-branch wiring, damp and wet locations • Washington State, IECC and MEC energy codes as tested per ASTM-E283 • Wet location listed with trims 11, 12, 4101, 4102 and 4181 • Wet location listed with trims 14 and 17 with outdoor rated PAR20 lamps • Conforms with City of Chicago IP requirements

Features

- 4" Housing
- Medium base porcelain socket with nickel-plated copper screw shell
- Vertically adjustable to accommodate up to a 1" ceiling thickness
- Aluminum housing is fully assembled for ease of installation
- Shipped with socket cap to protect against paint overspray
- Real Nail® 3 bar hangers: telescoping system with pre-installed removable nail for easy repositioning of housing in joist construction • Integral T-bar mounting feature for secure installation in suspended ceilings
 - Patented breakaway bars for tight joist spacing
 - Bar hangers may be re-positioned 90°
 - Curved foot facilitates alignment with joist bottom
 - Quick-Loc slot and oversized set screw lock fixture in position
- Pre-wired junction box with (6) 1/2" and (1) 3/4" knockouts with pryout slots, (4) non-metallic sheathed cable connectors, and ground wire
- Shadow-free, knife-edge trim design blends smoothly into the ceiling and allows architectural continuity with Aculux® trims
- UL Listed, C-UL/CSA certified for through-branch wiring, maximum (6) #12 AWG minimum 90° C branch circuit conductors (3 in, 3 out)
- Thermally protected against improper use of lamps
- Lamp wattage ratings and apertures based on trim selection. Trim selection follows IC1 and TC1 Series

Ordering Information

Catalog No.	Description
IC1	4" IC Incandescent housing
IC1S	IC1 with smaller footprint bar hanger (Real Nail® 2)
IC1W	IC1 with push-in electrical connectors for fast, secure installation

Ordering Information

Catalog No.	Description
GU10-WHIP	Medium base to GU10 base flexible socket adapter (use with 440 & 448 trims only)
T599	1" Socket Extender
4TSA	4" Housing adaptor converts original 4" housings for optimal retention of push-in style trims

Dimensions

