



Description

IC rated, energy efficient Air-Loc® sealed double wall construction housing does not require separate Air-Loc gasket • Can be completely covered with insulation • Air-Loc housing with all trims stops infiltration and exfiltration of air, reducing heating and cooling costs

Listings

UL Listed, C-UL/CSA certified for through-branch wiring, damp and wet locations • Washington State, IECC and MEC energy codes as tested per ASTM-E283 • Wet location listed with trims 11, 12, 4101, 4102 and 4181 • Wet location listed with trims 14 and 17 with outdoor rated PAR20 lamps • Conforms with City of Chicago IP requirements

Features

- 4" Housing
- Medium base porcelain socket with nickel-plated copper screw shell
- Vertically adjustable to accommodate up to a 1" ceiling thickness
- Aluminum housing is fully assembled for ease of installation
- Shipped with socket cap to protect against paint overspray
- Real Nail® 3 bar hangers: telescoping system with pre-installed removable nail for easy repositioning of housing in joist construction • Integral T-bar mounting feature for secure installation in suspended ceilings
 - Patented breakaway bars for tight joist spacing
 - Bar hangers may be re-positioned 90°
 - Curved foot facilitates alignment with joist bottom
 - Quick-Loc slot and oversized set screw lock fixture in position
- Pre-wired junction box with (6) 1/2" and (1) 3/4" knockouts with pryout slots, (4) non-metallic sheathed cable connectors, and ground wire
- Shadow-free, knife-edge trim design blends smoothly into the ceiling and allows architectural continuity with Aculux® trims
- UL Listed, C-UL/CSA certified for through-branch wiring, maximum (6) #12 AWG minimum 90° C branch circuit conductors (3 in, 3 out)
- Thermally protected against improper use of lamps
- Lamp wattage ratings and apertures based on trim selection. Trim selection follows IC1 and TC1 Series

Ordering Information

Catalog No.	Description
IC1	4" IC Incandescent housing
IC1S	IC1 with smaller footprint bar hanger (Real Nail® 2)
IC1W	IC1 with push-in electrical connectors for fast, secure installation

Ordering Information

Catalog No.	Description
GU10-WHIP	Medium base to GU10 base flexible socket adapter (use with 440 & 448 trims only)
T599	1" Socket Extender
4TSA	4" Housing adaptor converts original 4" housings for optimal retention of push-in style trims

Dimensions

